

DK20/DK20Q HYDRAULIC GARAGE JACK

2 Ton Hydraulic Garage Jack

- Jack for passenger cars and vans
- Very low minimum height of only 80 mm
- Wide and robust frame made of high-strength steel
- Precise and safe control while lowering
- Manual dead man's release for optimum safety when lowering
- Built-in safety overload valve
- Noiseless wheels incorporating a polyurethane central O-ring offers maximum surface protection
- Ergonomically designed handle ensuring positive and safe operation
- DK20Q is fitted with quick-lift pedal for easy reach of lifting point

Technical data	DK20/DK20Q	
Capacity	4400 lb	2,0 t
Min. height	3.15 in	80 mm
Max. height	19.49 in	495 mm
Frame length	25.98 in	660 mm
Handle length	37.40 in	950 mm
Frame height	6.30 in	160 mm
Width	16.14 in	410 mm
Weight	68 lb	31 kg



2347 Circuit Way Brooksville, FL 34604 352.799.1111 - sales@ameintl.net





