

EnviroNize® ULV



Strong injection and ultra-low volume spraying function ensures the penetration and diffusion to fine areas.



Applications

The **EnviroNize® ULV** has a wide array of applications, making it one of the most versatile and powerful ULV Sprayers on the market.

Disinfection | Sterilization

The **EnviroNize® ULV** enables injection of **EnviroNize® Disinfectant** solution to every area of its targeted disinfection. Its small micron droplet nozzle that is adjustable provides for complete coverage and protection against infectious pathogens.

Application | Spray

The **EnviroNize® ULV** is to be only used with **EnviroNize® Disinfectant** solution. The **EnviroNize® ULV** has a unique “open | close” valve providing ultimate spraying. The “Solution Flow” can easily be adjusted from releasing maximum solution when fully open to a reduced smaller micro flow when only slightly open. The **EnviroNize® ULV** can also be utilized as a “**blow dryer**” when the “open | close” is valve fully closed. In this setting the **EnviroNize® ULV** provides quick and immediate blow drying to areas such as electrical components and metals where applied solution should not be exposed to long periods of time.

FAST *and*
EFFICIENT

designed for
LARGER
SURFACE AREA
COVERAGE

1. Switch (On/Off - Slider) function control provides a gradual solution flow.
2. One-touch exchange of the solution tank.
3. Powerful Blower allows fast air drying as well as administering solution. Adjustable to 5-10 Micron droplet size.
4. CSA Approved 110V and 220V. Comes with a 3-liter solution reservoir.
5. Spray reaches 5-10 meters.
6. Long supply cord to allow for maximum coverage.

Features

Adjustable Settings



Ideal Setting

1. Adjust Spray Mist using "Adjustable Settings" Valve.
2. **Fine Mist (RECOMMENDED)** - Fully Close Valve then open 2 turns to maximum of 2.5 full turns.
3. Apply **EnviroNize® Disinfectant** solution 3 meters or 10 feet from target area with one pass to apply light non wet mist application.
4. Thoroughly **BLOW DRY** misted area within 1 minute so target area is dry and free of any moisture should mist encounter any electrical component or non-stainless-steel metals.

Flex Hose



Switch the Regular Nozzle



To the Flex Nozzle



Disinfect in ANY DIRECTION

Wet Setting

1. Adjust Spray using "Adjustable Settings" Open Valve.
2. **Wet Mist** (Non-Metal, Non-Electrical and Non-Painted Porous Surfaces) - Fully open the valve. This will provide maximum wetness. Adjust to desired wetness of spray by slightly closing the valve.
3. Apply **EnviroNize® Disinfectant** solution (Non-Metal, Non-Electrical and Non-Painted Porous Surfaces) 2 meters or 6 feet from target area. Let air dry.

Blow Dry

1. Adjust Spray using "Adjustable Settings" Valve and set to fully closed position. **BLOW DRY FEATURE:** To be used when misting near and on any metal, electrical components or high- tech lighting:
2. Fully Close the Valve (No Solution) - Turn **EnviroNize® ULV** to maximum on position to provide just air only **NO SOLUTION** - Thoroughly **BLOW DRY** misted area within 1 minute so target area is dry and free of any moisture.
3. Apply **BLOW DRY FEATURE** 1 meter or 3 feet from target area.

Care | Use



1. Fill the **Anolyte Tank** with **EnviroNize® Disinfectant** solution.
2. Adjust the settings using the "Adjustable Settings" valve to desired setting.
3. Apply **EnviroNize® Disinfectant** solution within recommended distance for each setting.

End of Day Maintenance (After Use)



AFTER USE (end of day) empty **EnviroNize® Disinfectant** solution back into the **EnviroNize® Disinfectant** container.



Partially fill the **ANOLYTE TANK** with clean potable water (hot preferred).



Reattach the **ANOLYTE TANK** to the **EnviroNize® ULV** to prepare for the end of day **FLUSHING STEP**.



Flushing Directions: Fully open the valve, run **EnviroNize® ULV** for 30 seconds to clear any granules which may lodge in the spray orifices.

ITEM	DESCRIPTION	CASE WEIGHT	UPC CODE	PACK SIZE	CASES FOR PALLET
ENVULVFOG	CORDED EnviroNize® ULV Sprayer Strong injection and ultra-low volume provide ultimate solution deployment	10.0 lbs 4.54 kg	N/A	1	N/A
ENVULV-TKN	3 Litre Extra Natural Solution Reservoir	1.5 lbs 0.68 kg	N/A	6	N/A



Distributed by EnviroNize®
 11-1673 Richmond St. PMB 110, London, ON, Canada N6G 2N3
 877.432.8548 | www.environize.ca | www.environize.us

