

MOBILE PIZZA OVEN

PZ-24-MB, PZ-36-MB & PZ-48-MB



Shown with front and end shelves

This is the Crown Verity Outdoor Mobile Pizza Oven. Now chefs can create exquisite pizzas in any outdoor environment.

The advanced pilot system along with each 12,500 BTUH burner, allow the oven to heat up quickly and stay lit in outdoor climates. The mobile pizza oven uses a special Volcanic Cooking Stone. This stone can absorb and maintain high heats and its smooth texture and low porosity prevents sticking.

The oven was designed to incorporate the three combinations of heat sources required to cook the perfect pizza: Direct, Convection and Radiant.

Each 12" cooking tile is independently temperature controlled, allowing the user to bake different food items or pizza types at the same time.

Keep peace of mind with Crown Verity's unsurpassed warranty including 1-year parts and labour, a 90-day replacement on cooking stones and 10-years replacement on the burners.

The Mobile Pizza Oven model is available as either liquid propane (LP) or natural gas (NG).

Project: _____

Item #: _____

Quantity: _____

SPECIFICATIONS

- Pizza Oven body and legs are made of 304 stainless steel
- 12,500 BTUH stainless steel burners and 5,000 BTUH Advanced Pilot System
- Two 14" wheels and two total lock casters
- Ready to use: ships completely assembled on a skid
- Tank holder(s) on back of unit that hold 20 lb. propane tank(s)
- Volcanic Cooking Stone absorbs and maintains the heat and its low porosity prevents sticking
- Includes crumb tray below the cooking stones and burners
- The dual dome system provides optimum temperature capture for a reliable and consistent heat
- c ETL us listed, Conforms to ANSI Z83.11/CSA 1.8 and NSF Standard 4

More Standard Features

- Unibody design for added strength
- Stainless steel pilot burner tube system
- Two stage regulator(s) and hose(s) on LP models
- Single gas connection and a 10 ft quick disconnect on NG models
- Removeable windguards
- Removable center finishing shelf
- Pizza oven door cover
- Factory technician tested prior to shipping
- 1 year parts and labor limited warranty
- 90-day replacement warranty on cooking stones and 10-year replacement on burners

Certifications



Options/Accessories

Front Shelf
End Shelf

Pizza Oven Cover

SPECIFICATIONS



| Model | PZ-24-MB | PZ-36-MB | PZ-48-MB |
|-----------------------|-----------------------|-----------------------|-----------------------|
| Number of Burners | 2 | 3 | 4 |
| BTUH | 30,000 | 42,500 | 55,000 |
| Actual Weight (lbs) | 274 | 342 | 425 |
| Shipping Weight (lbs) | 366 | 435 | 526 |
| Gas Connections (LP)* | 1 | 2 | 2 |
| Cooking Deck | 23.5" x 16" | 35.5" x 16" | 47.5" x 16" |
| Overall Dimensions | 46" L x 28" D x 53" H | 58" L x 28" D x 53" H | 70" L x 28" D x 53" H |

*All units are available in natural gas models (NG).

