

# TOWABLE GRILLS

TG-1, 2, 4

Project: \_\_\_\_\_  
Item #: \_\_\_\_\_  
Quantity: \_\_\_\_\_



TG-1

Our passion at Crown Verity is to bring the precision and performance of commercial kitchens to the outdoor environment. To that end we design and manufacture our grills to be reliable and go beyond traditional industry specifications.

Our grill bodies, cooking grates, burners, radiants, water pans, fasteners, pilot tubes are all constructed of 304 series stainless steel for durability and ease of cleaning. Compared to units made of metal or 430 stainless steel, our units are built to last.

15,000 BTUH stainless steel burners are placed every 5.75" to ensure the most even heat pattern possible. These units heat up to cooking temperature within 5 minutes. Our stainless steel burners and cooking grills carry a 10 year and lifetime warranty, respectively.

### Certifications



### SPECIFICATIONS

- 48" Gas grill constructed of 304 stainless steel including side shelves, trim, storage compartments, grids, burners and all fasteners
- 15,000 BTUH stainless steel burners
- Holds two 30 Lb. propane tanks (not included)
- TG-1 and TG-4 include two insulated storage compartments
- Includes water pan with drain ports to ease cleaning and help eliminate grease fires from occurring
- 16 ga stainless steel radiants that remain in place during transportation and cleaning
- Trailer conforms to all applicable motor vehicle safety standards
- c ETL us, ETL Sanitation listed, Conforms to ANSI Z83.11/CSA 1.8 and NSF Standard 4

### More Standard Features

- Stainless steel pilot burner tube system
- Ball size is 2" diameter, tongue weight is 50-180 Lbs. (varying load) depending on propane tank level and cooler load.
- 13" tire rims, 18" tire diameter
- Axle capacity 1500 Lbs.
- Standard 4 way flat trailer light hookup connector
- Trailer is transport Canada and U.S. DOT approved
- Swing away style front support jack with caster
- Factory technician tested prior to shipping
- 1 year parts and labor limited warranty
- Lifetime warranty on body and cooking grids and 10 years on burners

**SPECIFICATIONS**



Model	TG-1	TG-2	TG-4
<b>Number of Burners</b>	6	6	6
<b>BTUH</b>	99,000	99,000	99,000
<b>Actual Weight (lbs)</b>	852	652	1050
<b>Shipping Weight (lbs)</b>	1150	950	1400
<b>Payload capacity</b>	400 Lbs.		400 Lbs.
<b>Front Storage Compartment Dimensions</b>	N/A	N/A	50" W x 28.5"L
<b>Storage Compartment Dimensions</b>	Two X 42" L x 19" W x 15" D	N/A	Two X 42" L x 19" W x 15" D
<b>Portable Hot Water Dispenser</b>	N/A	N/A	1
<b>Single Hand Sink</b>	N/A	N/A	1
<b>Cooking Surface</b>	46" x 21"	46" x 21"	46" x 21"
<b>Overall Dimensions</b>	69" L x 124" D x 52" H	69" L x 124" D x 52" H	69" L x 155" D X 52" H

**Options/Accessories**

- |                     |               |
|---------------------|---------------|
| Adjustable Bun Rack | Griddle Plate |
| Steam Pan Adapter   | Rotisserie    |
| Wind Guard          | Smoker Box    |
| BBQ Cover           | Charcoal Tray |
| Propane Tanks       | Sink          |