

# UB 12E

## BLOWERS

**SURE FLAME**

### SPECIFICATIONS:

Fan Rating (CFM)

2,900

Static Pressure/CFM

0/2930

0.5/2720

0.75/2590

1/2440

1.5/2050

1.75/1780

Voltage

1Hp, 115V, 230V

Dimensions (LWH-inches)

17x24

Weight (lbs)

72



### FEATURES:

- Explosion proof blower
- CSA approved for Class 1 Group D hazardous locations
- Ductable on both ends (12" diameter)
- Powerful 1Hp motor
- 2,900 CFM fan rating
- Built-in handles for easy relocation
- Durable powder coated shell
- 3 year warranty\* (see [sureflame.ca/warranty](http://sureflame.ca/warranty))