

FN42C

FANS

SURE FLAME

SPECIFICATIONS:

Fan Rating (CFM)

14,000

Voltage

115V-9A, 1Ph

Dimensions (LWH-inches)

50x24x50

Weight (lbs)

210



FEATURES:

- Tough rental ready design
- 8" semi pneumatic wheels
- Easy one-person relocation
- 7 different air flow directional settings
- Low amp motor reduces energy draw
- Designed for quieter operation
- Durable powder coated shell
- 3 year warranty* (see sureflame.ca/warranty)