

MISTRAL 301 BL D2 is the perfect starter vacuum for light combustible dust. It's easy to carry around for general cleaning thanks to its compact size and overall user-friendliness.

Features

- ✓ Compact, portable and constructed with powder coated steel
- ✓ Spark-free brushless motor (up to 10,000 hour life expectancy)
- ✓ Bonding and grounding
- ✓ Tangential inlet with cyclone filter protector
- ✓ Removable stainless steel collection tank
- ✓ DUSTOP reverse pulse cleaning system
- ✓ Performance indicator light
- ✓ **NRTL certified for Class II, Division 2 hazardous locations**

Filtration

Primary Filter	Cartridge
Surface Area	6 ft ² (0.6 m ²)
Media Class (IEC 60335-2-69)	Antistatic Polyester - Class M
Cleaning System	DUSTOP

NRTL CERTIFIED FOR CLASS II, DIVISION 2

Groups F, G



Optionals

- Certified HEPA Class H14 (99.995% @ 0.18 µm)
- Partial or Full Stainless Steel Frame
- More Power Sources Available By Request
- Other Certifications Available By Request

MISTRAL 301 BL D2

Voltage	V - Hz	115 - 60 1~
Power	HP (kW)	1.5 (1.1)
Max Water Lift	inH2O (mmH2O)	90.6 (2300)
Max Max Airflow	CFM (m ³ /h)	121.8 (207)
Electrical Protection	IP Class	Explosion Proof
Capacity	gal (L)	4 (15)
Dimensions	in (WxLxH)	18 x 19 x 34
Weight	lbs (kg)	55 (25)
Noise Level (EN ISO 3744)	dB(A)	78
Suction Inlet	in (mm)	2 (50)