

MISTRAL 802 WD is a go-to vacuum for cleaning contractors and facilities burdened by a lot of liquid mixed with dust. Its steel body and motor head provide high resistance in industrial environments.

ATEX certified version available (Zones 1, 2, 21 & 22)



Features

- ✓ Compact, portable and constructed with powder coated steel
- ✓ 2 powerful bypass motors with independent cooling
- ✓ Interchangeable wet / dry filtration
- ✓ Liquid shut-off valve
- ✓ Large storage capacity
- ✓ Discharge system with hose

Filtration

Dry Filter Type	Bag
Dry Media	Nylon + Polyester / Class L
Dry Surface Area	9 ft ² (1 m ²)
Wet Filter Type	Bag
Wet Filter Media	Polypropylene (300 µm)
Wet Filter Surface Area	9 ft ² (1 m ²)

Optionals

- Cart Filter Kits (10-125 µm)
- Immersion Pump
- Partial or Full Stainless Steel Frame
- Earth Grounding
- ATEX Certified Version (Zones 1, 2, 21 & 22)
- More Power Sources Available By Request

MISTRAL 802 WD

Voltage	V - Hz	115 - 60 1~
Power	HP (kW)	2.7 (2.0)
Max Water Lift	inH ₂ O (mmH ₂ O)	90.1 (2289)
Max Airflow	CFM (m ³ /h)	211.9 (360)
Capacity	gal (L)	21 (80)
Dimensions	in (WxLxH)	21 x 23 x 42
Weight	lbs (kg)	88 (40)
Noise Level (EN ISO 3744)	dB(A)	76
Suction Inlet	in (mm)	3 (80)