



















DM 1 BL D2 is recognized as Delfin's most versatile single-phase vacuum for light-medium dust. NRTL tested and certified for Class II, Div. 2 environments, it adds an extra layer of safety and assurance.



## **Features**

- ✓ Compact, portable and constructed with powder coated steel
- ✓ Spark-free brushless motor (up to 10,000 hour life expectancy)
- √ Removable stainless steel collection tank
- ✓ Bonding and grounding
- ✓ Integrated cleaning system
- √ Cord wrap and accessory basket
- ✓ Performance indicator light
- √ NRTL certified for Class II, Division 2 hazardous locations

## **Filtration**

Primary Filter	Star	
Surface Area	32 ft <sup>2</sup> (3 m <sup>2</sup> )	
Media Class (IEC 60335-2-69)	Antistatic Polyester - Class M	
Cleaning System	Manual	

## **Optionals**

- Certified HEPA Class H14 (99.995% @ 0.18 μm)
- · Partial or Full Stainless Steel Frame
- More Power Sources Available By Request
- Other Certifications Available By Request

**DM 1 BL D2** 

Voltage	V - Hz	115 - 60 1~
Power	HP (kW)	1.5 (1.1)
Max Water Lift	inH2O (mmH2O)	90.6 (2300)
Max Airflow	CFM (m³/h)	121.8 (207)
Electrical Protection	IP Class	55
Capacity	gal (L)	26 (100)
Dimensions	in (WxLxH)	31 x 26 x 70
Weight	lbs (kg)	143 (65)
Noise Level (EN ISO 3744)	dB(A)	78
Suction Inlet	in (mm)	3 (80)