16 RETRO Series

COMMERCIAL HAND DRYER

CAST IRON CONSTRUCTION FOR COMPACT, STYLISH DESIGN WITH FAST DRYING SPEED AND LONG LASTING DURABILITY.


ENVIRONMENTALLY FRIENDLY, USING LESS THAN 1/6th OF THE ENERGY OF A CONVENTIONAL HAND DRYER

FEATURES

- Powerful
- Stylish appearance, blue LED
- Efficient, fast and safe
- Push button with long life operation
- Suitable to be installed in high traffic places
- LIFETIME warranty
- Small footprint
- Vandal proof
- Heavy duty reinforced steel
- Tamperproof screws
- Unique feature: drying timer customizable: from 0 to 3 minutes drying time

DIMENSIONS

FRONT VIEW



8-11/32" - 212mm

APPLICATIONS

- Washrooms and clean up areas, commercial facilities, factories, restaurants and hospitals
- High traffic areas
- Ideal for pools, gyms , stadiums (hair drying enable)



DISTANCE FROM BOTTOM EDGE OF DRYER TO FLOOR

	1		
Men	47" (119 cm)		
Women	44" (112 cm)		
Children 8-10 years	35″ (89 cm)		
Children 11-13 years	38″ (97 cm)		
Children 14-16 years	44" (112 cm)		
Disabled	36″ (91 cm)		

SIDE VIEW



Chrome



LIFETIME

SPECIFICATIONS

ORDERING GUIDE

Operation Voltage 110 – 120Vac, 50 – 60Hz, 2.0 – 2.4 KW 220 – 240Vac, 50 – 60Hz, 2.0 – 2.4 KW **Warm Air Speed Output** 28 m/s (62.6 miihr) **Drier Shall Deliver** 345 rrilh (202 CFM) **Motor Type** 200 W, 5,500 R.P.M., brush motor **Motor Thermal Protection** Auto resetting thermostat turns unit off at 105°C (221°F) **Heater Thermal Protection** Auto resetting thermostat turn units off at 65°C (14°F); Thermal fuse cut unit off at 141°C (28°F) **Drying Time** Approximately 20–25 seconds **Sound Level** 70±3 dB @ 1 m

TRO

Timing Protection 60 seconds auto shut off Drip Proof IPX1▲ Isolation Class 1 Material Steel Cover Finish Porcelain Enameled Coating Dimensions 281 mm (W) x 247 mm (H) x 212 mm (D) [11–1/16" (W) x 9–23/32" (H) x 8–11/32" (D)]

Model No.	Color	Watts	Volts Hz	Air Velocity LFM	Air Volume CFM	Noise dB	Dimensions (W x H x D) (mm/in.)	Weight (kg/lbs.)
RETRO-W110V			110-120,	10000	202	70	281X247X212	6.0.45
RETRO-W240V	White	2200	220-240	16000	202	70	(11X9X8)	6.8/15
RETRO-C110V			110-120,				281X247X212	
RETRO-C240V	Chrome	2200	220-240	16000	202	70	(11X9X8)	6.8/15



White