









- 


Touchless hands ON/OFF by infrared sensor
- 


Touchless operation to reduce cross-contamination and the spread of germs
- 

AA [LR6] alkaline batter
70,000 Cycles
- 

1100 ML
Front sight window makes it easy to check refill level
- 

Drop soap [Sanitizer]
1 ML gel per pump
- 

Spray medical alcohol
1 ML fog per pump
- 

Compact design with any washroom compliant
- 

Easy maintenance
Easy wall surface mounted
Anti-theft lockable

TECHNICAL DATA [GEL DISPENSER]

Motor	DC Motor, 1400 RPM, 0.5 W
Voltage:	DC 6V [4Pcs AA / LR6 Alkaline Battery]
Capacity:	1100 ML [37.2 OZ]
Dose/Pump:	1.0 ML [0.034 OZ]
Sensor Rang	3 -10 CM
Battery Life:	70,000 Cycles
Room Temperature:	5 - 40°C [41 - 104°F]
Drop Type:	Gel Soap or Gel Sanitizer
Body Material:	High Impact ABS Plastic
Unit Shipping W	0.9 KG [1.98 LB]
Unit Net Weight:	0.7 KG [1.54 LB]

TECHNICAL DATA [FOG DISPENSER]

Motor Type:	DC Motor, 1400 RPM, 0.5 W
Voltage:	DC 6V [4Pcs AA / LR6 Alkaline Battery]
Capacity:	1100 ML [37.2 OZ]
Dose/Pump:	1.0 ML [0.034 OZ]
Sensor Range:	3 -10 CM
Battery Life:	70,000 Cycles
Room Temperature:	5 - 40°C [41 - 104°F]
Spray Type:	Medical Alcohol Fog
Body Material:	High Impact ABS Plastic
Unit Shipping Weight:	0.9 KG [1.98 LB]
Unit Net Weight:	0.7 KG [1.54 LB]

COMAC N24X ALCOHOL [SANITIZER] DISPENSER

ADVANTAGE

- Touch-free Comac hand soap [sanitizer] dispenser.
- Touchless operation to reduce cross-contamination and the spread of germs.
- The most HYGIENIC soap dispensing solution. Coated with A24 antibacterial
- Sight window makes it easy to check refill level.
- Multiple colors and finishes available.
- Enable significant cost savings, reduce labor.
- Made of durable plastic, the keyed system helps reduce pilferage.

MADE IN CANADA

