GLOBAL®
globalindustrial.com

Facial Recognition & Body Temperature Camera System
Specifications

Model 708528: Counter Stand
Model 708529: 3'H Floor Mount
Model 708530: 4'H Floor Mount



Features:

- ***Ultra-thin 8" wide LCD screen***
- ***Real time body temperature readings***
- ***Face recognition; supports 30,000 user faces***
- ***Mask recognition***
- ***Accuracy: ± 0.5°F***
- ***Elevated temperature detection with alarm***
- ***Records facial identification and temperature information***
- ***Available in 3 different size mounting stands***
- ***Built-in WiFi module, can be used as hotspot and WiFi connection.***
- ***Great for use in areas including hotels, office buildings, schools, entrance gates, and other areas where face access control is required***

Computer Requirements: Windows 7/8/9/10

Specifications:

Sensor:	Thermal Imaging Infrared Temperature Sensor
Temperature Range:	95 - 108°F; ±0.5° (35 - 42°C; ±0.3°)
Display:	8" LCD
Recognition Distance:	1.6 to 16 ft.
Response Time:	≤ 0.3 Second
Memory Data:	30,000 Faces
Camera:	2 MP
Lens:	1:2.8, Focal Length .07", Field of View: 118°
Dynamic:	≥ 105dB
Signal to Noise Ratio:	≥ 35dB
White Balance:	Auto, Indoor, Outdoor, Sodium Lamp Mode, Manual
Video:	H.265 Main Profile / H.264 High profile / M-JPEG
Max Resolution:	800 x 1280 @ 30fps
Output Bit Rate:	Auto, Indoor, Outdoor, Sodium Lamp Mode, Manual
Audio Compression:	G711, PCM
USB Interface:	(1) USB
Device Storage:	8G
Power:	DC12V 2A
Interfaces:	Rich Hardware, Integrated 100M Ethernet, Audio, Wiegand, Relay, USB
Mounting Stand Options:	Counter Stand, 3'H Mount or 4'H Mount
Connection:	Ethernet, Wifi, Hotspot
Operating System:	Linux OS
Access Record Capacity:	5 million (without photos)
Product Dimensions:	9-1/2" x 5-1/3" x 1"
Weight:	2 lbs.



Model 708528



Model 708529



Model 708530

For more information visit globalindustrial.com or call 1-800-645-1232.

GLOBAL
globalindustrial.com