

# Buffing Wheels – IB-8 / IB-10

## SPECIFICATIONS – IB-8

Wheel Size	8" x 1/2" x 5/8"
Wheel Type	Spiral and Half Spiral
Shaft Diameter	5/8"
Spacer Sizes	1/2", 1", 2"
Motor HP	1-1/2"
Motor Speed	3,600 rpm
Power Requirements	115V
Decibels	75dB @ 3'
Foot Print	9-1/2" x 8-1/16"
Distance between Mounting Holes	8-1/2"
Shipping Dimensions	27" x 11" x 12"
Shipping Weight	50 lbs.

Specifications subject to change without notice.

- ◆ 8" buffer/polisher
- ◆ 3600 rpms
- ◆ LED light included
- ◆ Enclosed pre-lubricated ball bearings
- ◆ Rubber mounts
- ◆ 2 extra pairs of flange washers included
- ◆ 115V



IB-8

## SPECIFICATIONS – IB-10

Wheel Size	10" x 1" x 1"
Wheel Type	Spiral and Half Spiral
Shaft Diameter	1"
Spacer Sizes	1/2", 1", 2"
Motor HP	1-1/2"
Motor Speed	1,800 rpm
Power Requirements	115V
Decibels	75dB @ 3'
Foot Print	10" x 9-5/8"
Distance between Mounting Holes	8-3/4"
Shipping Dimensions	34" x 13" x 15-1/2"
Shipping Weight	85 lbs.

Specifications subject to change without notice.

- ◆ 10" buffer/polisher
- ◆ 1800 rpms
- ◆ LED light included
- ◆ Enclosed pre-lubricated ball bearings
- ◆ Rubber mounts
- ◆ 2 extra pairs of flange washers included
- ◆ 115V
- ◆ CSA Certified



IB-10