

Disc & Belt Grinders – DBG-9436



SPECIFICATIONS – BG-9436

Disc Diameter	9"
Disc Grits	80
Disc Table Size	11-13/16" x 5-29/32"
Disc Table Tilt	45 degrees down
T-Slot Size	3/4" x 3/8"
Dust Port	2"
Belt Size	36" x 4"
Belt Grit	80
Belt Speed (SFPM)	3769
Belt Drive Wheel	4" x 4"
Belt Table Tilt	45 Degrees Down
Belt Table Size	6-5/16" x 3"
Dust port	2"
Motor HP	1"
Motor Speed	3,600 rpm
Power Requirements	115V
Decibels	75dB @ 3'
Foot Print	9-1/2" x 8-1/16"
Distance between Mounting Holes	8-1/2"
Shipping Dimensions	22" x 25" x 17"
Shipping Weight	100 lbs.

Specifications subject to change without notice.

- ◆ Combination belt grinder and sanding disc
- ◆ 9" sanding disc
- ◆ 4" x 36" grinding belt
- ◆ 3600 rpms
- ◆ Enclosed pre-lubricated ball bearings
- ◆ Rubber mounts
- ◆ Adjustable tool rests
- ◆ Work light included
- ◆ CSA listed
- ◆ 115V