

Box & Pan Brakes – BB-4814 / BB-4812



BB-4814

- ◆ 48" x 14-gauge capacity
- ◆ Counterweight apron assist
- ◆ Adjustable beam
- ◆ Floor stand included
- ◆ 2-piece hardened finger assortment: 6-3", 2-4", 1-25"
- ◆ Angle stop rod and counterweight assist

SPECIFICATIONS – BB-4814		
Length	48"	1220 mm
Thickness (SS)	14 ga. (18 ga.)	
Bend Angle	0 – 135°	
Box Depth	4"	101.6 mm
Finger Sizes	3" – 4" – 25"	
Stand	Yes	
Shipping Dimensions (L x W x H)	69" x 31" x 36"	1753 x 787 x 914 mm
Shipping Weight	1,276 lbs.	580 kgs.

Specifications subject to change without notice.

SPECIFICATIONS BB-4812		
Length	48"	1220 mm
Thickness (SS)	12 ga. (16 ga.)	
Bend Angle	0 – 135°	
Finger Sizes	3" – 4" – 5" – 6"	
Beam Adjustment	1"	25.4 mm.
Min. Reverse Bend	.625"	16 mm
Box Depth	6"	152 mm
Shipping Dimensions (L x W x H)	71" x 34" x 44"	1803 x 864 x 1118 mm
Shipping Weight	1,980 lbs.	900 kgs.

Specifications subject to change without notice.

- ◆ 48" x 12-gauge capacity
- ◆ Box, pan, and straight
- ◆ 2-piece hardened finger assortment: 3-3", 2-4", 5-5", 1-6"
- ◆ Angle stop rod and counterweight assist



BB-4812