

Box & Pan Brakes – BB-4012F

- ◆ Foot operated material clamping
- ◆ Enables easy material adjustment
- ◆ Stop rod for repeatable bending
- ◆ Finger assortment
(1 pc. each size): 1", 1-1/8",
1-3/8", 1-1/2", 1-3/4", 2", 3", 4",
6", 7-3/4", 10-5/8"
- ◆ .033" finger radius

SPECIFICATIONS – BB-4012F		
Length	40"	1016 mm
Thickness (SS)	12 ga. (16 ga.)	
Bend Angle	0 – 135°	
Max. Clamping Bar Lift (foot operated)	1.85"	47 mm
Box Depth	2.5"	63.5 mm
Shipping Dimensions (L x W x H)	58" x 25" x 50"	1473 x 635 x 1270 mm
Shipping Weight	705 lbs.	320 kgs.

Specifications subject to change without notice.

