

Box & Pan Brakes – BB-12016 / BB-12014



BB-12016

- ◆ Heavy duty
- ◆ Bend angle indicator and stop rod for repeatability
- ◆ Adjustable counterweights for apron lift assist
- ◆ Adjustable beam for varying sheet thickness
- ◆ Sturdy floor stand
- ◆ 2-piece hardened finger assortment: 6-3", 4-4", 10-5", 6-6"
- ◆ 6" box depth

SPECIFICATIONS BB-12016		
Length	120"	3048 mm
Thickness (SS)	16 ga. (20 ga.)	
Bend Angle	0 – 135°	
Finger Sizes	3" – 4" – 5" – 6"	
Beam Adjustment	1"	25.4 mm.
Min. Reverse Bend	.625"	16 mm
Box Depth	6"	152 mm
Shipping Dimensions (L x W x H)	146" x 34" x 46"	3708 x 864 x 1168 mm
Shipping Weight	3,190 lbs.	1450 kgs.

Specifications subject to change without notice.



BB-12014

- ◆ Heavy duty
- ◆ Bend angle indicator and stop rod for repeatability
- ◆ Adjustable counterweights for apron lift assist
- ◆ Adjustable beam for varying sheet thickness
- ◆ Sturdy floor stand
- ◆ 2-piece hardened finger assortment: 6-3", 4-4", 10-5", 6-6"
- ◆ 6" box depth

SPECIFICATIONS BB-12014		
Length	120"	3048 mm
Thickness (SS)	14 ga. (18 ga.)	
Bend Angle	0 – 135°	
Finger Sizes	3" – 4" – 5" – 6"	
Beam Adjustment	1"	25.4 mm.
Min. Reverse Bend	.625"	16 mm
Box Depth	6"	152 mm
Shipping Dimensions (L x W x H)	146" x 34" x 48"	3708 x 864 x 1118 mm
Shipping Weight	3,410 lbs.	1550 kgs.

Specifications subject to change without notice.