

Ironworkers – HP-160

SPECIFICATIONS – HP-160		
Max. Punching Capacity	.314"	4.775 mm
Throat Depth	6.25"	159 mm
Power	Manual	
Shipping Dimensions (L x W x H)	20.5" x 9" x 36.6"	521 mm x 229 mm x 927 mm
Shipping Weight	176 lbs.	80 kgs.

Specifications subject to change without notice.

- ◆ Adjustable material stop
- ◆ Nine sets of punches and dies included
- ◆ Extra long handle for increased leverage
- ◆ Includes round punches and dies for 1/8", 3/16", 1/4", 5/16", 3/8", 7/16", 1/2", 9/16", and 5/8"



**HP-160
Hand Punch**

