

Manual Band Saws – BS-127P / BS-128M

SPECIFICATIONS – BS-127P

| Capacity (90°/45°) | | |
|---------------------------------|--|-----------------------------------|
| Round | 5" / 3" / 1.65" | 127 mm / 78 mm / 42 mm |
| Square | 5" / 3" / 1.65" | 127 mm / 78 mm / 42 mm |
| Rectangular | 5.31" x 5" / 3" x 6.75" / 1.65" x 2.9" | 135 x 127 / 78 x 172 / 42 x 75 mm |
| Blade Size (H x W x L) | .5" / .025" / 56.69" | 13 mm / .65 mm / 1440 mm |
| Blade Speed (fpm) | 75–246 Variable | |
| Miter Angle | 0 – 60° | |
| Miter Adjustment | Swivel Head | |
| Descent Control | n/a | |
| Return | Manual | |
| Drive | Gear | |
| Motor | .5 hp | |
| Power | 110V | |
| Shipping Dimensions (L x W x H) | 28" x 15" x 18" | 711 x 381 x 457 mm |
| Shipping Weight | 56 lbs. | 26 kgs. |

Specifications subject to change without notice.

- ◆ Portable
- ◆ Variable speed
- ◆ Head miterers up to 60°
- ◆ 5" round capacity
- ◆ 110V



BS-127P

- ◆ Horizontal or vertical operation
- ◆ 1/2" blade
- ◆ Swivel head, single miter
- ◆ Hydraulic and manual descent
- ◆ Wheeled stand and lift bar for easy mobility
- ◆ 110V



BS-128M

SPECIFICATIONS – BS-128M

| Capacity (90°/60°/45°) | | |
|---------------------------------|-------------------------------------|--|
| Round | 5" / 1.75" / 3.75" | 127 mm / 44 mm / 95 mm |
| Rectangular | 5" x 6" / 1.75" x 2.19" / 3" x 3.7" | 127 x 152 mm / 44 x 55 mm / 76 x 93 mm |
| Blade Size (H x W x L) | .50" / .023" / 64.48" | 12.7 mm / .584 mm / 1637 mm |
| Blade Speed (fpm) | 78 / 154 / 200 | |
| Miter Angle | 0 – 60° | |
| Miter Adjustment | Swivel Head | |
| Descent Control | Hydraulic | |
| Return | Manual | |
| Drive | Belt | |
| Motor | .75 hp | |
| Power | 110V | |
| Shipping Dimensions (L x W x H) | 38" x 22" x 25" | 965 x 559 x 635 mm |
| Shipping Weight | 319 lbs. | 145 kgs. |

Specifications subject to change without notice.