

Hydraulic H-Frame Presses – HSP-75A / HSP-100A

| SPECIFICATIONS – HSP-75A | | |
|---------------------------------|--------------------|----------------------|
| Maximum Capacity | 75 tons | 67 ton |
| Working Width | 31.5" | 800 mm |
| Movable Cylinder | Yes | Yes |
| Cylinder Stroke | 9.8" | 249 mm |
| Cylinder Diameter | 9" | 228 mm |
| Piston Rod Diameter | 3.5" | 89 mm |
| Piston Head Diameter | 3" | 76.2 mm |
| Power | Pneumatic / Manual | |
| Shipping Dimensions (L x W x H) | 83" x 44" x 24" | 2108 x 1118 x 610 mm |
| Shipping Weight | 1,300 lbs. | 590 kgs. |

Specifications subject to change without notice.

- ◆ 75 ton
- ◆ Pneumatic/manual operation
- ◆ Foot pedal control
- ◆ Movable cylinder
- ◆ Automatic piston return
- ◆ Table winch
- ◆ Pressure gauge
- ◆ Includes vee-blocks
- ◆ 100 – 123 psi, 9 cfm

- ◆ 100 ton
- ◆ Pneumatic/manual operation
- ◆ Foot pedal control
- ◆ Movable cylinder
- ◆ Automatic piston return
- ◆ Table winch
- ◆ Pressure gauge
- ◆ Includes vee-blocks
- ◆ 100 – 123 psi, 9 cfm

| SPECIFICATIONS – HSP-100A | | |
|---------------------------------|--------------------|----------------------|
| Maximum Capacity | 100 tons | 89 tons |
| Working Width | 31" | 787 mm |
| Movable Cylinder | Yes | Yes |
| Cylinder Stroke | 11.8" | 300 mm |
| Cylinder Diameter | 6.5" | 165 mm |
| Piston Rod Diameter | 4" | 101 mm |
| Piston Head Diameter | 3.5" | 89 mm |
| Power | Pneumatic / Manual | |
| Shipping Dimensions (L x W x H) | 86" x 45" x 24" | 2184 x 1143 x 610 mm |
| Shipping Weight | 1,705 lbs. | 775 kgs. |

Specifications subject to change without notice.



HSP-75A



HSP-100A