

# Hydraulic H-Frame Presses – HSP-10H / HSP-20A

SPECIFICATIONS – HSP-10H		
Maximum Capacity	10 tons	9 tons
Working Width	13.5"	343 mm
Movable Cylinder	Yes	Yes
Cylinder Stroke	7"	178 mm
Cylinder Diameter	5.11"	130 mm
Piston Rod Diameter	1.5"	38 mm
Piston Head Diameter	2"	50.8 mm
Power	Manual	
Shipping Dimensions (L x W x H)	60" x 44" x 11"	1524 x 1118 x 279 mm
Shipping Weight	150 lbs.	68 kgs.

Specifications subject to change without notice.

- ◆ 10 ton
- ◆ Hand operated
- ◆ Fixed cylinder
- ◆ Automatic piston return
- ◆ Pressure gauge
- ◆ Includes vee-blocks
- ◆ 1/16" ram movement per pump
- ◆ 24" x 20" x 36" tall

**HSP-10H**



**HSP-20A**

- ◆ 20 ton
- ◆ Pneumatic/manual operation
- ◆ Movable cylinder
- ◆ Automatic piston return
- ◆ Pressure gauge
- ◆ Includes vee-blocks
- ◆ 100 – 123 psi, 9 cfm

SPECIFICATIONS – HSP-20A		
Maximum Capacity	20 tons	18 tons
Working Width	19.25"	489 mm
Movable Cylinder	Yes	Yes
Cylinder Stroke	7.5"	190.5 mm
Cylinder Diameter	3"	76.2 mm
Piston Rod Diameter	2"	50.8 mm
Piston Head Diameter	2"	50.8 mm
Power	Pneumatic / Manual	
Shipping Dimensions (L x W x H)	68" x 44" x 24"	1727 x 1118 x 610 mm
Shipping Weight	319 lbs.	145 kgs.

Specifications subject to change without notice.

