

Roll Benders – R-M3 / R-M5

SPECIFICATIONS – R-M3

Capacities		
Solid Round	.25"	6.35 mm
Flat Bar	1" x .1875"	25.4 mm x 4.763 mm
Minimum Diameter	3"	76.2 mm
Handle Length	13.5"	343 mm
Power Requirement	Manual	
Shipping Dimensions (L x W x H)	15" x 7" x 8"	381 mm x 178 mm x 203 mm
Shipping Weight	18 lbs.	8 kgs.

Specifications subject to change without notice.



R-M3



R-M5

- ◆ Small compact and portable
- ◆ 3 driven rolls
- ◆ Manually powered
- ◆ Includes tooling for flat bar, 1/4" and 1/2" round
- ◆ Perfect for doing small circles
- ◆ Includes heavy duty stand
- ◆ Optional tooling sets for round stock available

SPECIFICATIONS – R-M5

Capacities		
Solid Round (with optional tooling)	.5"	12.7 mm
Flat Bar	1" x .187"	25.4 mm x 4.75 mm
Minimum Diameter	2.75"	70 mm
Handle Length	9"	229 mm
Power Requirement	Manual	
Shipping Dimensions (L x W x H)	30" x 40" x 18"	762 mm x 1016 mm x 458 mm
Shipping Weight	85 lbs.	38 kgs.

Specifications subject to change without notice.

OPTIONAL TOOLING

SKU	Description
Tube Tooling	
1007593	1/4" Round Tube Rolls for R-M5
1010069	3/8" Round Tube Rolls for R-M5
1007577	1/2" Round Tube Rolls for R-M5