

Hydraulic H-Frame Presses –HSP-30A / HSP-50A

SPECIFICATIONS – HSP-30A		
Maximum Capacity	30 tons	27 tons
Working Width	22.5"	571.5 mm
Movable Cylinder	Yes	Yes
Cylinder Stroke	5.9"	150 mm
Cylinder Diameter	4.5"	114 mm
Piston Rod Diameter	3.5"	89 mm
Piston Head Diameter	2.375"	60 mm
Power	Pneumatic / Manual	
Shipping Dimensions (L x W x H)	76" x 44" x 24"	1930 x 1118 x 610 mm
Shipping Weight	450 lbs.	205 kgs.

Specifications subject to change without notice.

- ◆ 30 ton
- ◆ Pneumatic/manual operation
- ◆ Movable cylinder
- ◆ Automatic piston return
- ◆ Pressure gauge
- ◆ Includes vee-blocks
- ◆ 100 – 123 psi, 9 cfm



- ◆ 50 ton
- ◆ Pneumatic/manual operation
- ◆ Foot pedal control
- ◆ Movable cylinder
- ◆ Automatic piston return
- ◆ Table winch
- ◆ Pressure gauge
- ◆ Includes vee-blocks
- ◆ 100 – 123 psi, 9 cfm

SPECIFICATIONS – HSP-50A		
Maximum Capacity	50 tons	45 tons
Working Width	28.5"	723 mm
Movable Cylinder	Yes	Yes
Cylinder Stroke	7.8"	200 mm
Cylinder Diameter	6"	152 mm
Piston Rod Diameter	3.5"	89 mm
Piston Head Diameter	2.75"	70 mm
Power	Pneumatic / Manual	
Shipping Dimensions (L x W x H)	83" x 44" x 24"	2108 x 1118 x 610 mm
Shipping Weight	803 lbs.	365 kgs.

Specifications subject to change without notice.

