

Arbor Presses – AP-3R / AP-5

SPECIFICATIONS – AP-3R		
Capacity	3 tons	2.7 tons
Ram Size	1.5"	38 mm
Throat Depth	5"	127 mm
Maximum Material Height	11"	279 mm
Power	Manual	
Shipping Dimensions (L x W x H)	18" x 9" x 25"	457 x 229 x 635 mm
Shipping Weight	132 lbs.	60 kgs.

Specifications subject to change without notice.

- ◆ Ratcheting action
- ◆ Square ram for greater strength
- ◆ Rigid cast frame
- ◆ Includes 4-position die plate
- ◆ Die openings 7/8", 1-1/4", 1-3/4", and 2-1/8"

AP-3R



SPECIFICATIONS – AP-5		
Capacity	5.6 tons	5 tons
Maximum Arbor Height	2.75"	70 mm
Ram Size	2" x 2"	50 mm x 50 mm
Throat Depth	8.89"	225.8 mm
Maximum Material Height	15.75"	400 mm
Power	Manual	
Shipping Dimensions (L x W x H)	30" x 15" x 37.5"	762 x 381 x 953 mm
Shipping Weight	365 lbs.	166 kgs.

Specifications subject to change without notice.

- ◆ Adjustable handle for increased leverage
- ◆ Square ram for greater strength
- ◆ Rigid cast frame
- ◆ Includes 4-position die plate
- ◆ Die openings 3/4", 1-3/8", 1-3/4", and 2-1/2"

AP-5

