

Metal Dust Collectors – MDC-3500-HD

SPECIFICATIONS – MDC-3500-HD

| | | |
|---------------------------------|-----------------------|---------------------------|
| Air Capacity | 2340 CFM | |
| Noise | 78 dB | |
| Filter | HEPA Cartridge | |
| Filter Size | Ø15" x 26"L | Ø380 mm x 660 mm |
| Inlet Size | 10" | 354 mm |
| Motor | 5 hp | |
| Power Requirements | 230 V Three Phase | |
| Shipping Dimensions (L x W x H) | 38.2" x 39.2" x 75.6" | 969.9 x 994.4 x 1917.6 mm |
| Shipping Weight | 550 lbs. | 250 kgs. |

Specifications subject to change without notice.

- ◆ Heavy duty metalworking dust collector
- ◆ 5 hp
- ◆ 2340 CFM
- ◆ Pulse clean filter cartridge system
- ◆ Fire resistant teflon coated filter
- ◆ Magnehelic pressure gauge
- ◆ Full steel construction
- ◆ HEPA filter standard
- ◆ Tool-less filter maintenance
- ◆ CSA – U.S. certified
- ◆ 220V 3 phase



Cartridge filter



Filter removal



Hepa filter