

Stomp Shears – SF-5216E / SF-5216

SPECIFICATIONS – SF-5216E		
Shear Length	52"	1321 mm
Thickness (SS)	16 ga. (20 ga.)	
Front Gauge Length	20"	508 mm
Back Gauge Length	33"	838 mm
Blade Angle	1°	
Power Requirements	Manual	
Shipping Dimensions (L x W x H)	66" x 30" x 46"	1676 x 762 x 1168 mm
Shipping Weight	1,199 lbs.	545 kgs.

Specifications subject to change without notice.

- ◆ High-carbon, high-chromium blades
- ◆ Front support arms with squaring bar
- ◆ Spring assisted operation
- ◆ 4 sided blades
- ◆ Back gauge include
- ◆ Finger guard



SF-5216E



SF-5216

SPECIFICATIONS – SF-5216		
Shear Length	52"	1321 mm
Thickness (SS)	16 ga. (20 ga.)	
Front Gauge Length	24"	609 mm
Back Gauge Length	24"	609 mm
Blade Angle	1°	
Power Requirements	Manual	
Shipping Dimensions (L x W x H)	67" x 32" x 53"	1702 x 813 x 1346 mm
Shipping Weight	996 lbs.	454 kgs.

Specifications subject to change without notice.

- ◆ 52" x 16-gauge mild steel capacity
- ◆ Back and side gauges
- ◆ Finger guard
- ◆ Heavy duty frame
- ◆ Foot shear
- ◆ 4 sided blades