

# Box & Pan Brakes – BB-4816E / BB-4816

SPECIFICATIONS – BB-4816E		
Length	48"	1220 mm
Thickness (SS)	16 ga. (20 ga.)	
Bend Angle	0 – 135°	
Box Depth	1.57"	40 mm
Stand	Yes	
Shipping Dimensions (L x W x H)	46" x 19" x 27"	1168 x 483 x 686 mm
Shipping Weight	360 lbs.	164 kgs.

Specifications subject to change without notice.

- ◆ Stop rod for repeatability
- ◆ Counterweight apron assist
- ◆ Adjustable beam for varying sheet thickness
- ◆ Floor stand included
- ◆ 16-finger assortment: 5-2", 6-3", 5-4"



BB-4816E

SPECIFICATIONS BB-4816		
Length	48"	1219 mm
Thickness (SS)	16 ga. (20 ga.)	
Bend Angle	0 – 135°	
Box Depth	4"	101.6 mm
Finger Sizes	2" – 3" – 4"	
Beam		
Adjustment	.625"	16 mm
Lift (max.)	1.75"	44 mm
Stand	Yes	
Shipping Dimensions (L x W x H)	64" x 27" x 32"	1626 x 686 x 813 mm
Shipping Weight	550 lbs.	250 kgs.

Specifications subject to change without notice.

- ◆ 48" x 16-gauge mild steel capacity
- ◆ Includes floor stand
- ◆ Stop rod and counterweight assist
- ◆ 16-finger assortment: 5-2", 6-3", 5-4"



BB-4816