

Manual Band Saws – BS-712M / BS-712MS



BS-712M

- ◆ 110V
- ◆ Cuts metal and more
- ◆ 3/4" blade standard
- ◆ Hydraulic descent
- ◆ 3-speeds
- ◆ Direct drive
- ◆ Horizontal and vertical cutting capabilities
- ◆ 220V optional



SPECIFICATIONS – BS-712M		
Capacity (90°/45°)		
Round	7" / 4.33"	177 mm / 110 mm
Rectangular	7" x 10.23" / 4.72" x 4.13"	177 x 259 mm / 119 x 104 mm
Blade Size (H x W x L)	.75" / .035" / 92.91"	19 mm / .9 mm / 2360 mm
Blade Speed (fpm)	125 / 215 / 270	
Blade Guide	Roller	
Miter Angle	0 – 45°	
Miter Adjustment	Vise	
Table Height	22"	558 mm
Descent Control	Hydraulic	
Return	Manual	
Drive	Gear	
Motor	1 hp	
Power	110V / 220V, 1-Phase	
Shipping Dimensions (L x W x H)	51" x 18" x 42"	1295 x 457 x 1067 mm
Shipping Weight	300 lbs.	136 kgs.

Specifications subject to change without notice.

SPECIFICATIONS – BS-712MS		
Capacity (90°/45°)		
Round	7" / 4.33"	177 mm / 110 mm
Rectangular	7" x 10.23" / 4.72" x 4.13"	177 x 259 mm / 119 x 104 mm
Blade Size (H x W x L)	.75" / .035" / 92.91"	19 mm / .9 mm / 2360 mm
Blade Speed (fpm)	125 / 215 / 270	
Blade Guide	Roller	
Miter Angle	0 – 45°	
Miter Adjustment	Swivel Head	
Table Height	23"	584 mm
Descent Control	Hydraulic	
Return	Manual	
Drive	Gear	
Motor	1 hp	
Power	110V / 220V, 1-Phase	
Shipping Dimensions (L x W x H)	51" x 23" x 43"	1295 x 584 x 1092 mm
Shipping Weight	397 lbs.	181 kgs.

Specifications subject to change without notice.

- ◆ 110V
- ◆ Cuts metal and more
- ◆ 3/4" blade standard
- ◆ Hydraulic descent
- ◆ 3-speeds
- ◆ Direct drive
- ◆ Horizontal and vertical cutting capabilities
- ◆ Single mitering (swivel)
- ◆ 220V optional



BS-712MS