

# Straight Hand Brakes – HB-9616 / HB-9612

## SPECIFICATIONS – HB-9616

Capacity		
Length	96"	2438 mm
Thickness (SS)	16 ga. (20 ga.)	
Max. Opening	2.08"	53 mm
Bend Angle	0 – 135°	
Beam Adjustment	1"	25.4 mm.
Min. Reverse Bend	.625"	16 mm
Shipping Dimensions (L x W x H)	123" x 34" x 40"	3124 x 864 x 1016 mm
Shipping Weight	1,650 lbs.	750 kgs.

Specifications subject to change without notice.

- ◆ 96" x 16-gauge mild steel capacity
- ◆ Includes floor stand
- ◆ Stop rod and counterweight assist



HB-9616

## SPECIFICATIONS – HB-9612

Capacity		
Length	96"	2438 mm
Thickness (SS)	12 ga. (16 ga.)	
Max. Opening	2.08"	53 mm
Bend Angle	0 – 135°	
Beam Adjustment	1"	25.4 mm.
Min. Reverse Bend	.625"	16 mm
Shipping Dimensions (L x W x H)	123" x 34" x 40"	3124 x 864 x 1016 mm
Shipping Weight	2,640 lbs.	1204 kgs.

Specifications subject to change without notice.

- ◆ 96" x 12-gauge mild steel capacity
- ◆ Includes floor stand
- ◆ Stop rod and counterweight assist



HB-9612