

# Manual Shears – MPS-2 / MPS-5

SPECIFICATIONS – MPS-2		
Shear Capacity	10 ga.	
Shear Length	2.5"	63.5 mm
Blade Length	4.25"	108 mm
Power Requirements	Manual	
Shipping Dimensions (L x W x H)	24" x 24" x 24"	610 x 610 x 610 mm
Shipping Weight	50 lbs.	23 kgs.

Specifications subject to change without notice.

- ◆ Throatless — Design
- ◆ 10-gauge mild steel capacity
- ◆ 4-1/4" blade length
- ◆ Perfect for Radius corners



MPS-2

- ◆ Throatless — Design
- ◆ 3/16" mild steel capacity
- ◆ 5-1/4" blade length
- ◆ Perfect for Radius corners
- ◆ Includes material hold down

SPECIFICATIONS – MPS-5		
Shear Capacity	3/16"	5 mm
Shear Length	3"	76.2 mm
Blade Length	5.25"	133 mm
Power Requirements	Manual	
Shipping Dimensions (L x W x H)	24" x 24" x 24"	610 x 610 x 610 mm
Shipping Weight	75 lbs.	34 kgs.

Specifications subject to change without notice.



MPS-5