

Box & Pan Brakes – BB-7212 / BB-9612

SPECIFICATIONS BB-7212

Length	72"	1830 mm
Thickness (SS)	12 ga. (16 ga.)	
Bend Angle	0 – 135°	
Finger Sizes	3" – 4" – 5" – 6"	
Beam Adjustment	1"	25.4 mm
Min. Reverse Bend	.625"	16 mm
Box Depth	6"	152 mm
Shipping Dimensions (L x W x H)	97" x 34" x 44"	2464 x 864 x 1118 mm
Shipping Weight	2,420 lbs.	1100 kgs.

Specifications subject to change without notice.

- ◆ 72" x 12-gauge capacity
- ◆ Heavy duty
- ◆ Bend angle indicator and stop rod for repeatability
- ◆ Adjustable counterweights for apron lift assist
- ◆ Adjustable beam for varying sheet thickness
- ◆ Sturdy floor stand
- ◆ 2-piece hardened finger assortment: 6-3", 3-4", 6-5", 2-6"
- ◆ 6" box depth



BB-7212

SPECIFICATIONS BB-9612

Length	96"	2438 mm
Thickness (SS)	12 ga. (16 ga.)	
Bend Angle	0 – 135°	
Finger Sizes	3" – 4" – 5" – 6"	
Beam Adjustment	1"	25.4 mm.
Min. Reverse Bend	.625"	16 mm
Box Depth	6"	152 mm
Shipping Dimensions (L x W x H)	123" x 34" x 46"	3124 x 864 x 1168 mm
Shipping Weight	3,220 lbs.	1460 kgs.

Specifications subject to change without notice.

- ◆ 96" x 12-gauge capacity
- ◆ Heavy duty
- ◆ Bend angle indicator and stop rod for repeatability
- ◆ Adjustable counterweights for apron lift assist
- ◆ Adjustable beam for varying sheet thickness
- ◆ 2-piece hardened finger assortment 6-3", 4-4", 10-5", 2-6"
- ◆ 6" box depth



BB-9612