

Straight Hand Brakes – HB-12016 / HB-12014



HB-12016

SPECIFICATIONS – HB-12016		
Capacity		
Length	120"	3048 mm
Thickness (SS)	16 ga. (20 ga.)	
Max. Opening	2.08"	53 mm
Bend Angle	0 – 135°	
Beam Adjustment	1"	25.4 mm.
Min. Reverse Bend	.625"	16 mm
Shipping Dimensions (L x W x H)	148" x 34" x 40"	3759 x 864 x 1016 mm
Shipping Weight	2,860 lbs.	1300 kgs.

Specifications subject to change without notice.

- ◆ 120" x 16-gauge mild steel capacity
- ◆ Includes floor stand
- ◆ Stop rod and counterweight assist



HB-12014

SPECIFICATIONS – HB-12014		
Capacity		
Length	120"	3048 mm
Thickness (SS)	14 ga. (18 ga.)	
Max. Opening	2.08"	53 mm
Bend Angle	0 – 135°	
Beam Adjustment	1"	25.4 mm.
Min. Reverse Bend	.625"	16 mm
Shipping Dimensions (L x W x H)	148" x 34" x 40"	3759 x 864 x 1016 mm
Shipping Weight	3,300 lbs.	1500 kgs.

Specifications subject to change without notice.

- ◆ 120" x 14-gauge mild steel capacity
- ◆ Includes floor stand
- ◆ Stop rod and counterweight assist