

Straight Hand Brakes – HB-4816E / HB-4816



HB-4816E



HB-4816

SPECIFICATIONS – HB-4816E

Capacity		
Length	48"	1220 mm
Thickness (SS)	16 ga. (20 ga.)	
Bend Angle	0 – 135°	
Shipping Dimensions (L x W x H)	63" x 16" x 23"	1600 x 406 x 584 mm
Shipping Weight	450 lbs.	204 kgs.

Specifications subject to change without notice.

- ◆ 48" x 16-gauge mild steel capacity
- ◆ Includes floor stand
- ◆ Stop rod for repeatability
- ◆ Adjustable clamping pressure
- ◆ 2-1/4" minimum bend depth

SPECIFICATIONS – HB-4816

Capacity		
Length	48"	1220 mm
Thickness (SS)	16 ga. (20 ga.)	
Bend Angle	0 – 135°	
Shipping Dimensions (L x W x H)	63" x 16" x 23"	1600 x 406 x 584 mm
Shipping Weight	506 lbs.	230 kgs.

Specifications subject to change without notice.

- ◆ 48" x 16-gauge mild steel capacity
- ◆ Stop rod for repeatability
- ◆ Counterweight apron assist
- ◆ Adjustable beam for varying sheet thickness
- ◆ Sturdy floor stand
- ◆ Adjustable clamping pressure
- ◆ 2-1/4" minimum bend depth