

# Ironworkers – SW-22M-P

SPECIFICATIONS – SW-22M-P		
Shear Capacity Flat	4" x 5/16"	100 mm x 8 mm
Shear Capacity Plate	1/4"	6 mm
Shear Capacity Round	5/8"	15.8 mm
Shear Capacity Square	5/8"	15.8 mm
Shear Capacity Angle	2-3/8" x 1/4"	60 mm x 6 mm
Throat Depth	6.25	158.75 mm
Maximum Punching Capacity	.314"	8 mm
Power	Manual	
Shipping Weight	345 lbs.	(157 kgs.)
Dimensions (L x W x H)	39" x 16" x 26"	990 x 400 x 600 mm

Specifications subject to change without notice.

- ◆ Combines HP-160 and SW-22M into one compact machine
- ◆ Made from plate steel
- ◆ Extra-long handle for more leverage
- ◆ Shear station shears angle, flat, T-bar, round, and square stock
- ◆ Includes material hold downs
- ◆ Includes round punches and dies for 1/8", 1/16", 1/4", 5/16", 3/8", 7/16", 1/2", 9/16", and 5/8"

