

# Ornamental Metal Forming – MPB-10 / MPB-15

## SPECIFICATIONS – MPB-10

Capacity		
Round	.394"	10 mm
Flat Bar	1.180" x .394"	30 mm x 10 mm
Square	.394"	10 mm
Shipping Dimensions (L x W x H)		
	36" x 20" x 15"	914 x 508 x 381 mm
Shipping Weight		
	50 lbs.	23 kgs.

Specifications subject to change without notice.

- ◆ Scroll bender
- ◆ Includes 3" and 7" tooling
- ◆ Bench-mounted
- ◆ 3", 5" and 7" scroll die



MPB-10



MPB-15

## SPECIFICATIONS – MPB-15

Capacity		
Round	.590"	15 mm
Flat Bar	1.180" x .314"	30 mm x 8 mm
Square	.511"	13 mm
Scroll Capacity	.375"	9.5 mm
Shipping Dimensions (L x W x H)		
	20" x 13" x 9"	508 x 330 x 228 mm
Shipping Weight		
	52 lbs.	24 kgs.

Specifications subject to change without notice.

- ◆ Bend rolls, hoops, and coils
- ◆ Works with round, square, and flat stock
- ◆ Bench-mounted
- ◆ 3" diameter pin
- ◆ 90° bend die
- ◆ 5-1/4" scroll