

Tube & Pipe Notchers – TN-50M / TN-125M / TN-200M

SPECIFICATIONS – TN-50M		
Notching Capacity (Pipe)	1/4", 3/8", 1/2"	6.3 mm, 9.525 mm, 12.7 mm
Power Requirements	Manual	
Shipping Dimensions (L x W x H)	20" x 7" x 7"	508 mm x 178 mm x 178 mm
Shipping Weight	17 lbs.	8 kgs.

Specifications subject to change without notice.

- ◆ Will notch 1/4", 3/8", and 1/2" pipe at 90°
- ◆ Manually operated



TN-50M

SPECIFICATIONS – TN-125M		
Notching Capacity (Pipe)	3/4", 1", 1-1/4"	19 mm, 25.4 mm, 31.75 mm
Power Requirements	Manual	
Shipping Dimensions (L x W x H)	20" x 7" x 7"	508 mm x 178 mm x 178 mm
Shipping Weight	20 lbs.	9 kgs.

Specifications subject to change without notice.

- ◆ Will notch 3/4", 1", and 1-1/4" pipe at 90°
- ◆ Manually operated



TN-125M

SPECIFICATIONS – TN-200M		
Notching Capacity (Pipe)	1-1/2", 2"	38.1 mm, 50.8 mm,
Power Requirements	Manual	
Shipping Dimensions (L x W x H)	20" x 7" x 7"	508 mm x 178 mm x 178 mm
Shipping Weight	36 lbs.	16 kgs.

Specifications subject to change without notice.

- ◆ Will notch 1-1/2" and 2" pipe at 90°
- ◆ Manually operated



TN-200M