# AF 990CT



# COLD TEMPERATURE ALL SERVICE JACKET TAPE

### TYPICAL APPLICATIONS

• For use in cold and dual temperature systems to seal, seam and join scrim-reinforced pipe and duct insulation

### PRODUCT FEATURES

- Linered
- Superior stability during extreme fluctuations in temperature
- Tear-resistant backing that matches white duct and pipe insulation
- Permanent bond, cold temperature acrylic adhesive with excellent shelf life

### CONSTRUCTION

Overall Grade/Function: HVAC duct and pipe insulation Backing: White kraft paper/scrim/foil (ASJ) DECA free Adhesive: Cold temperature, white, acrylic-based

Liner: Non-contaminating, siliconized, flat, white, paper release liner

### STANDARD WIDTH(S)

72 mm 96 mm

## STANDARD LENGTH(S)

46 n

Contact your Shurtape sales representative for other available sizes

## **APPLICABLE STANDARDS**

Tested in accordance with UL 723; FSI 5/SDI 10

# STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

### COLOR(S)



PHISICAL PROPERTIES	SIANDARD	MEIKIC
Tensile Strength	50 lbs/in width	87.6 N/10 mm
Adhesion to Stainless Steel	80 oz/in width	8.76 N/10 mm
Thickness (With Liner)	12.6 mils	0.32 mm
Thickness (Without Liner)	8.3 mils	0.21 mm
Elongation	6.7%	6.7%
Service Temperature Range	-20 F to 260 F	-29 C to 127 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

