## **Indoor/Outdoor UL507 Certified Wall, Ceiling or Pole Mount Fan**

The Indoor/Outdoor POW (Premium Outdoor Waterproof) fan from J&D Manufacturing is a durable, three-speed, waterproof fan. These fans come pre-wired for 115 Volts with an 8' cord and 3-prong plug for no electrician+ required installation.

These fans are perfect in areas around the farm that may come in contact with rain, humidity, and water spray.



- 18" model available in white or black
- High output performance
- 3-speed pull chain
- Attached 8' cord with 3-prong plug pre-wired for 115 Volts
- Versatile powder coated mounting bracket allows for easy tilt and swivel of fan to easily change direction and angle of air movement, a perfect work station fan
- UL507 certified for indoor and outdoor use
- Aluminum blades
- Direct drive quiet operation
- · Corrosion resistant, powder coated fan guards meet OSHA 1910.212(a)(5) requirements for installation at any height
- Totally enclosed, maintenance-free, high-efficiency motors have completely sealed ball bearings, UL and CUL recognized, and are covered by a 1 Year Warranty
- Rated for use with our misting/fogging products to increase cooling abilities

	Part#	Size	Ph	Spd	Thrust CFM	- /	Drive	Prop
	Single Phase							
	White							
	POW14	14"	1	3(H)	1,090	13.6	Direct	3-Alm
				(M)	1,000	15.2		
				(L)	870	15.5		
	POW18	18"	1	3(H)	2,210	13.9	Direct	3-Alm
				(M)	1,870	13.4		
				(L)	1,420	12.7		
	Black							
*	POW18B	18"	1	3(H)	2,210	13.9	Direct	3-Alm
				(M)	1,870	13.4		
				(L)	1,420	12.7		
	Optional	al Bracket						
	POWTPB Bracket, Post/Pole, White Powder Co w/U-bolt & Hdwr							at,
	* Pact callers/recommended models							

Best sellers/recommended models

Bold red text is data based on testing performed by an accredited lab using ANSI/AMCA Standard 230-12

+ GFCI (Ground Fault Circuit Interrupter) recommended on all circuits



**POWTPB** - Optional Bracket for post or pole