## Indoor/Outdoor UL507 Certified Oscillating Wall Mount Fan

The Indoor/Outdoor Wall Mount POW (Premium Outdoor Waterproof) fan from J&D Manufacturing is an oscillating, three-speed, waterproof fan with quiet operation. The POW Wall Mount fan includes a wall mount bracket and an attached 10' cord pre-wired for 115 volts so no electrician is required.

These fans are perfect in areas around the farm that may come in contact with rain, humidity, and water spray.

\*GFCI (Ground Fault Circuit Interrupter) recommended on all circuits

## **Features**

- Available in 24" and 30"
- Includes powder coated steel wall bracket
- High output performance and quiet operation
- 3-speed pull chain
- Attached 10' cord with 3-prong plug pre-wired for 115 Volts
- Range of oscillation 93°
- UL507 certified for indoor and outdoor use
- Aluminum blades painted
- Corrosion resistant, powder coated fan guards meet OSHA 1910.212(a)(5) requirements for installation at any height
- Totally enclosed, maintenance-free, direct drive high-efficiency motors have completely sealed ball bearings, UL and CUL recognized, and are covered by a 1 Year Warranty
- Rated for use with our misting/fogging products to increase cooling abilities
- Minimal assembly required

	Part#	Size	Ph	Spd	Thrust CFM	Thrust CFM/ Watt	Drive	Prop
	Single Phase							
*	POW24OSC	24"	1	3(H)	3,470	13.1	Direct	3-Alm
				(M)	2,930	16.3		
				(L)	2,550	16.4		
	POW30OSC	30"	1	3(H)	4,790	17.7	Direct	3-Alm
				(M)	3,960	20.6		
				(L)	3,310	20.7		

- \* Best sellers/recommended models
- Variable speed fans require separate variable speed control to adjust fan speed

Bold red text is data based on testing performed by an accredited lab using ANSI/AMCA Standard 230-12



▲WARNING: This product can expose you to chemicals including chromium, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov/product.