

# Poly Stormer

Keep air moving efficiently across your facility with J&D's Poly Stormer. Made with high CFM in mind, this economical fan will give you the efficiency you want and the air flow you deserve.

## Features

- Fan ships fully assembled and ready for installation
- Direct drive motor with no belts or bearings to maintain
- Totally enclosed, maintenance-free, high-efficiency standard motors have completely sealed ball bearings, UL and CUL recognized, and are covered by a **2 Year Warranty**
- Gold Star motors have a **3 Year Warranty**
- Polyethylene housing will not rust or corrode
- Stainless steel fasteners, powder coated guards, and galvanized prop for long lasting corrosion resistance
- Light weight for easier installation
- Motors have built in automatic thermal overload protection for the longest motor life possible
- Compatible with our misting/fogging product line



RECIRCULATION FANS

| Part#               | Size | Ph | Spd    | Thrust CFM   | Thrust CFM/Watt | Drive  | Prop  |
|---------------------|------|----|--------|--------------|-----------------|--------|-------|
| <b>Single Phase</b> |      |    |        |              |                 |        |       |
| VPS36A-GS           | 36"  | 1  | 1      | <b>8,450</b> | <b>17.1</b>     | Direct | 3-Glv |
| <b>Three Phase</b>  |      |    |        |              |                 |        |       |
| * VPS36CF-GS        | 36"  | 3  | 1/Var^ | <b>8,560</b> | <b>18.9</b>     | Direct | 3-Glv |



| Part#               | Size | Ph | Spd | Thrust CFM   | Thrust CFM/Watt | Drive  | Prop  |
|---------------------|------|----|-----|--------------|-----------------|--------|-------|
| <b>Single Phase</b> |      |    |     |              |                 |        |       |
| VPS36A              | 36"  | 1  | 1   | <b>8,210</b> | <b>16.3</b>     | Direct | 3-Glv |
| <b>Three Phase</b>  |      |    |     |              |                 |        |       |
| VPS36CF             | 36"  | 3  | 1   | <b>8,460</b> | <b>18.7</b>     | Direct | 3-Glv |

\* Best sellers/recommended models

^ Variable speed fans require separate variable speed control to adjust fan speed

**Bold red text is data based on testing performed by an accredited lab using ANSI/AMCA Standard 230-12**

**OSHA requires this fan to be mounted a minimum of 7' above the floor**

All Poly Stormer fans include a hot dip galvanized mounting bracket



# High Output Deluxe Basket Fan

J&D Manufacturing's High Output Deluxe Basket Fan Series combines high performance, economical pricing and energy efficiency to give you one of the best valued fan series available on the market today.

## Features

- Fan ships completely assembled and ready for installation
- Direct drive - no belts or pulleys to maintain
- Heavy gauge, corrosion resistant black powder coated guards
- Single phase models include attached cord with 3-prong plug pre-wired for 115 Volts
- Guards meet OSHA 1910.212(a)(5) requirements allowing this fan to be installed at any height
- Totally enclosed, maintenance-free, high-efficiency motors feature sealed ball bearings and are covered by a **2 Year Warranty**
- Compatible with our misting/fogging product line



| Part#  | Size | Ph | Spd | Thrust CFM   | Thrust CFM/Watt | Drive  | Prop  |
|--|------|----|-----|--------------|-----------------|--------|-------|
| <b>Single Phase</b>  |      |    |     |              |                 |        |       |
| <b>With Cord</b> (pre-wired for 115V, electrician may rewire for 230V) |      |    |     |              |                 |        |       |
| VDB20  | 20"  | 1  | 1   | <b>3,340</b> | <b>9.1</b>      | Direct | 3-Alm |
| VDB24  | 24"  | 1  | 1   | <b>5,370</b> | <b>10.8</b>     | Direct | 3-Alm |
| VDB30  | 30"  | 1  | 1   | <b>6,500</b> | <b>11.4</b>     | Direct | 3-Alm |
| VDB36  | 36"  | 1  | 1   | <b>9,520</b> | <b>17.3</b>     | Direct | 3-Glv |

| Part#              | Size | Ph | Spd | Thrust CFM   | Thrust CFM/Watt | Drive  | Prop  |
|--------------------|------|----|-----|--------------|-----------------|--------|-------|
| <b>Three Phase</b> |      |    |     |              |                 |        |       |
| <b>No Cord</b>     |      |    |     |              |                 |        |       |
| VDB303             | 30"  | 3  | 1   | <b>6,730</b> | <b>13.0</b>     | Direct | 3-Alm |
| * VDB363           | 36"  | 3  | 1   | <b>9,500</b> | <b>19.4</b>     | Direct | 3-Glv |

\* Best sellers/recommended models

All High Output Deluxe Basket fans include a hot dip galvanized mounting bracket



**Bold red text is data based on testing performed by an accredited lab using ANSI/AMCA Standard 230-12**

**⚠ WARNING:** This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov/product](http://www.P65Warnings.ca.gov/product).