
Mega Fan Series

72" Fiberglass Exhaust Fans


Whether trying to select fans that meet requirements for energy rebates, specific ventilation requirements, or zero maintenance, J&D's Mega Fan Series of 72" Fiberglass Exhaust Fans has a model that will fit all of your exhaust fan needs.



▲ WARNING: This product can expose you to chemicals including chromium, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov/product.

Mega Storm Fans

Belt Drive 72" Fiberglass Exhaust Fan



Shown: Mega Storm II (Mega Storm motor belt tensioner appearance and locations differ)

- Twin Gates[®] size "A" belts are easily accessible and require no tools for replacement in seconds
- Double groove steel belt tensioner for longer life
- 1½" shaft and sealed pillow block bearings
- 3 Year Warranty on bearings

					@ 0.10" SP				
		_				CFM/			
	Part #		Ph	Spd	CFM	Watt	Drive	Prop	
	Mega Storm II								
	Three Phase								
	With 1 Piece Cone (for 3 piece cone, add H after C in part #)								
	Aluminum Shutter								
	VMA72A5C33	72"	3	1	39,270	20.4	Belt	5-Alm	
	VMA72A5C33-E	72"	3	1	40,121	21.1	Belt	5-Alm	
*	VMA72A5C33-H	72"	3	1	47,330	16.9	Belt	5-Alm	
	Mega Storm								
	Single Phase								
	No Cone								
	Aluminum Shu	tter							
	VMSA72A5N31	72"	1	1	38,960	14.9	Belt	5-Alm	
	With 1 Piece C	one (for 3	piece	cone, add	H after C	in part	#)	
	Aluminum Shu								
*	VMSA72A5C31	72"	1	1	40,792	15.7	Belt	5-Alm	
	Three Phase								
	No Cone								
	Aluminum Shu	tter							
	VMSA72A5N33	72"	3	1	42,950	14.3	Belt	5-Alm	
	With 1 Piece C	one (for 3						
	Aluminum Shutter								
	VMSA72A5C33	72"	3	1	44,734	14.9	Belt	5-Alm	
	* Best sellers/recommended models								

* Best sellers/recommended models

Bold red text is data based on testing performed by an accredited lab using ANSI/AMCA 210-07 standard.



High Performance & High Efficiency Models Available

Mega Storm II Features

- 47,330 CFM @.10"SP high performance model available
- High efficiency model that exceed 21 CFM/Watt
- 3 Year Warranty on Energy efficient (-E) and High efficient (-H) motors

Mega Storm Features

- Certified performances up to 44,734 CFM @.10" SP
- Single or three phase 3 HP, UL recognized motors
- 2 Year Warranty on motors

▲ WARNING: This product can expose you to chemicals including chromium, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov/product.