



Product name

Sales display for 2-jaw pullers

For removing bearings, gears, discs, etc.

Art. No. 20-ST+

Series 20-ST+

EAN 4021176668944



	Technical attribute	Metric	Imperial
	Spread	90 - 250 mm	4 - 9 7/8 inch
	Depth	100 - 200 mm	3 7/8 - 7 7/8 inch
	Spread used internal	70 - 340 mm	2 3/4 - 13 3/8 inch
	Hexagon drive (male)	17-27 mm	
	Maximum torque	80 - 300 Nm	
max.	Maximum load	4,5 - 8,5 t	4.5 US t
	Weight	20.2 kg	
	Number of jaws	2	2



Technologies



GLIDE & FIX

The improved geometry guarantees quick and easy movement of the jaws on the cross-beam.



ARMLOCK

The cross-legged jaws guarantee maximum stability for suspending the jaws in the slider.



QUICK ADJUST

The knurls allow the jaws to be quickly released and moved on the cross-beam without the need for tools.



SWITCH

A two-sided spindle tip provides optimal adjustment of the spindle to the shaft.



Spare part

Art. No.	Product name
20-1+	Universal 2-jaw puller with quick adjusting jaws
20-10+	Universal 2-jaw puller with quick adjusting jaws
20-2+	Universal 2-jaw puller with quick adjusting jaws
20-20+	Universal 2-jaw puller with quick adjusting jaws
20-3+	Universal 2-jaw puller with quick adjusting jaws
20-STL	Stand

Content

Art. No.	Product name
20-1+	Universal 2-jaw puller with quick adjusting jaws
20-10+	Universal 2-jaw puller with quick adjusting jaws
20-2+	Universal 2-jaw puller with quick adjusting jaws
20-20+	Universal 2-jaw puller with quick adjusting jaws
20-3+	Universal 2-jaw puller with quick adjusting jaws
20-STL	Stand