



Product name *

Universal 3-jaw puller with long hydraulic spindle and quick adjusting jaws (including mechanical pressure screw)

For pulling particularly tight bearings, gears, discs, etc.

Art. No. 30-30+B

Series 30+B

EAN 4021176303067



	Technical attribute	Metric	Imperial
	Spread	50 - 375 mm	2 - 14 3/4 inch
	Depth	200 mm	7 7/8 inch
	Spread used internal	180 - 440 mm	7 1/8 - 17 3/8 inch
	Hexagon drive (male)	36 mm	
	Maximum torque	250 Nm	
	Maximum load	15 t	16 US t
	Weight	12.475 kg	
	Space below	6,5 mm	1/4 inch
	Space next to it	52 mm	2 1/16 inch
	Number of jaws	3	3



Technologies



GLIDE & FIX

The improved geometry guarantees quick and easy movement of the jaws on the cross-beam.



ARMLOCK

The cross-legged jaws guarantee maximum stability for suspending the jaws in the slider.



QUICK ADJUST

The knurls allow the jaws to be quickly released and moved on the cross-beam without the need for tools.



SWITCH

A two-sided spindle tip provides optimal adjustment of the spindle to the shaft.



HYDRAULIC

Pullers with hydraulic function.



Spare part

Art. No.	Product name
8-02	Long hydraulic spindle
3-202-S	3 quick adjusting jaws (set)
11-0-T	Cross-beam

Also included in

Art. No.	Product name
WT-010	Puller product range - commercial vehicles - TOP