



Item # RS-CAMO-300W

Description

50in CAMO Series CREE LED Light Bar 300W/20,000LM - While Supplies last

Categories Truck, Powersports, LED Light Bars

Sub-Categories LED Light Bars, CAMO Series Dual Row LED Light Bars, Camouflage Dual Row Light Bars

UPC 00811712027328 Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition Manufacturer EZ Category

New

Race Sport Lighting

Harmonization Code Universal Life Expectancy

8512.20.2080

YES

SEMA Product Light Bar

Reverse Polarity Operating Voltage Current Draw

Wattage Chip Type IP Rating LUX

300-Watts

Kelvin (Color Temperature) Beam Pattern Lumens Universal or Vehicle Specific

6,500K

20,000lm

Universal

Made In Warranty M.S.R.P. M.A.P.

China

3 year

\$651.00

\$375.99



Product Information

An expansion on our street series line, these camouflage style LED light bars use their camo coating to easily blend in with nature. Perfect for hunting trips or for off road vehicles.

- 300W/20,000 LM (3W per diode)
- Spot Style Optics
- 23.8 Amps
- 50,000 hour life span
- 12-24v voltage range
- Color Temperature: 6500K
- Waterproof Certified: IP67
- Operation Temp: -40°C-80°C
- Bar Measures 52" End to End w/ Brackets
- Lens Measures 50" End to End
- Mount to Mount measurement is 55"
- Durable Camouflage Coating
- 3 Year Warranty

Part # 1004292 Est. Labor

Part Type ID 1069

Gross Weight 15.70 Width 5.500

Net Weight 15.50 Height 6.000

DIM Weight 12.34 Depth 52.00

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

www.racesportinc.com