



Item # RS-CREE-10BARHD

Description

12in Heavy Duty Series CREE Combo Bar 60W/4,200LM

Categories Truck, Powersports, Agricultural, Jeep, LED Light Bars

Sub-Categories LED Light Bars, Heavy Duty PROFESSIONAL Series Dual Row LED Light Bars - Lifetime Warranty, Heavy Duty

UPC 00811712024181 Unit of Measure EA

Related Skus:

Cross Sell Skus:

Condition Manufacturer EZ Category
 New Race Sport Lighting HD Series Dual Row Light Bars

Harmonization Code Universal Life Expectancy
 8512.20.2080 YES 50,000 hours

SEMA Product Light Bar

Reverse Polarity Operating Voltage Current Draw
 12-32VDC 5.7A

Wattage Chip Type IP Rating LUX
 60-Watts CREE IP68

Kelvin (Color Temperature) Beam Pattern Lumens Universal or Vehicle Specific
 6,500K Combo 4,200lm Universal

Made In Warranty M.S.R.P. M.A.P.
 China Lifetime \$394.00 \$227.99



Product Information

Premium light bars for serious off-roading and demanding situations.

These bars will take punishment and never let you down

- 60W/4,200 LM (3W per diode)
- Combination Flood/Spot Optics
- 5.7 Amps
- 50,000 hour lifetime
- 6,500 Kelvin color
- 12V-32V capable
- IP68 Waterproof Rated
- Bar Measures 12" End to End w/ Brackets
- Lens Measures 10" End to End
- Mount to Mount measurement is 15"
- Super efficient LED driver
- Special optics improve light projection
- Perfect for off-road, emergency, and public use
- Lifetime Warranty

Part # 1004301 Est. Labor
Part Type ID 1069
Gross Weight 5.200 Width 13.50
Net Weight 5.200 Height 5.250
DIM Weight 2.677 Depth 5.250

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.