GLOBAL INDUSTRIAL™
We can supply that.®

Lab Refrigerator Undercounter, Glass Door, 2.4 Cu Ft.
Specifications

Model 2453700



Features:

- ***High Accuracy Temperature Control***
- ***LED Display***
- ***Lockable Design***
- ***Audible and Visual Alarms: high/low temperature; power failure; door ajar; sensor error; low battery remote system.***
- ***Air Cooling Auto Defrost***
- ***Energy Efficient Hydrocarbon (HC) Refrigeration System***
- ***Adjustable Feet or Casters***

Specifications

Cabinet Type:	Upright; Glass Door
Capacity:	2.4 Cu. Ft.
Temperature Range:	2 to 8°C (35.6 to 46.4°F)
Refrigerant:	R600a
Noise:	41 dBA
Display:	LED
Controller:	Microprocessor
Defrost Mode:	Auto
Power Supply:	115/60 (V/Hz)
Power:	150W
Electrical Current:	1.7A
Cooling Type:	Forced Air Cooling
Exterior Dimensions (WxDxH):	19.5” x 22.8” x 26.0”
Interior Dimensions (WxDxH):	16.3” x 15.2” x 19.9”
Product Weight:	83.8 lbs.
# Shelves/Baskets:	2/1
Certifications:	CE; UL/cUL