



MST Digital Magnetic Stirrers

Small and powerful magnetic stirrer with digital display, timer
and auto-reverse



Reliable and Precise

The MST Digital is equipped with a bright digital display to easily set up the stirring speed. By turning the knob is possible to set the correct speed with 10 rpm steps.

- Powerful brushless motor ensuring premium resistance over time
- Speed regulation up to 1500 rpm
- SpeedServo™ technology ensuring constant speed counter reacting to viscosity changes
- Accepts up to 5 liter flasks
- Bright digital display for accurate speed monitoring
- On board timer for unattended operations
- Auto reverse of the stirring direction to ensure better mixing
- Technopolymer guarantees high resistance to chemicals



INSTRUMENT - CODE

MST Digital

100-240 V / 50-60 Hz

F203A0450

TECHNICAL DATA

CONSTRUCTION MATERIAL	Technopolymer
STIRRING VOLUME	Up to 5 L
ELECTRONIC SPEED REGULATION	Up to 1500 rpm
SPEED CONTROL	Excellent speed control even at low revolutions
COUNTER REACTION	Constant Speed
TIMER	From 1 to 900 minutes; continuous mode
AUTO-REVERSE	From 5 to 900 seconds
LOCK FUNCTION	Yes
INTERMITTENT MODE	Yes
STIRRING SYSTEM	PCM magnet
MOTOR	Brushless
DIMENSION (WXHXD)	120x50x145 mm (4.7x1.97x5.9 in)
POWER	0.6 W
WEIGHT	0.6 Kg (1.3 lb)



We reserve the right to make technical alterations
We do not assume liability for errors in printing, typing or transmission

VELP Official Partner

DESIGNED AND MANUFACTURED IN ITALY



ITALY - HQ
Via Stazione 16
20865 Usmate (MB) Italy
Tel. +39 039 628811
velpitalia@velp.com

INDIA
velpindia@velp.com

USA
155 Keyland Court, Bohemia
NY 11716 - U.S.
Tel. +1 631 573 6002
velpusa@velp.com

CHINA
Xinlong Rd Building 28, Lane 1333
Shanghai city - China
Tel. +86 180 1755 7329
velpchina@velp.com