



CLASSIC

Vortex Mixer

Compact vortex mixer suitable for different mixing requirements,
with touch or continuous mode



Compact, Robust and Convenient

Compact vortex mixer suitable for different mixing requirements, with touch or continuous mode. It is highly resistant to chemicals and has 3 anti-slip rubber feet for stability.

- Automatic start in touch mode or continuous operation
- Variable speed operation, electronically controlled up to 3000 rpm
- Optimum resistance to chemicals from technopolymer casing
- Excellent stability with zinc alloy base
- IP 42 protection against particles and liquids



INSTRUMENT - CODE

CLASSIC

100-240 V / 50-60 Hz

F202A0173

* Included: Mixing cup head

TECHNICAL DATA

CONSTRUCTION MATERIAL	Zinc alloy and technopolymer
SUPPORT SYSTEM	3 anti-sliding feet
OPERATIONAL MODE	Touch / Continuous
SPEED SETTING	Analog
SPEED CONTROL	Electronic
STIRRING SPEED	0 - 3000 rpm
ORBITAL DIAMETER	4,5 mm
TYPE OF MOVEMENT	Orbital
ELECTRONIC PROTECTION DEGREE CEI EN 60529	IP 42
POWER	15 W
WEIGHT	2.2 Kg (4.9 lb)
DIMENSIONS (WxHxD)	180x70x220 mm (7.1x2.8x8.7 in)



We reserve the right to make technical alterations
We do not assume liability for errors in printing, typing or transmission

VELP Official Partner

DESIGNED AND MANUFACTURED IN ITALY



ITALY - HQ
Via Stazione 16
20865 Usmate (MB) Italy
Tel. +39 039 628811
velpitalia@velp.com

INDIA
velpindia@velp.com

USA
155 Keyland Court, Bohemia
NY 11716 - U.S.
Tel. +1 631 573 6002
velpusa@velp.com

CHINA
Xinlong Rd Building 28, Lane 1333
Shanghai city - China
Tel. +86 180 1755 7329
velpchina@velp.com