



# ZX3

## Vortex Mixer

---

Vortex mixer with adjustable stirring speed,  
with touch or continuous mode



# Reliable and Universal

Reliable vortex mixer with adjustable stirring speed, touch or continuous mode. ZX3 features large, anti-slip rubber feet to ensure maximum stability. It is also highly resistant to chemicals.

- Automatic start in touch mode or continuous operation
- Variable speed operation, electronically controlled up to 3000 rpm
- Optimum resistance to chemicals from technopolymer casing
- Excellent stability with zinc alloy base
- IP 42 protection against particles and liquids



## INSTRUMENT - CODE

<b>ZX3 *</b>	100-240 V / 50-60 Hz	<b>F202A0176</b>
<b>ZX3 and Foam Stands **</b>	100-240 V / 50-60 Hz	<b>SA202A0176</b>

\* Included: Mixing cup head

\*\* Included: ZX3 Vortex Mixer, Stand for 19 microvials Eppendorf 1,5 ml, Customizable soft foam top, Small rubber supporting plate Ø 50 mm, Mixing cup head

## TECHNICAL DATA

CONSTRUCTION MATERIAL	Zinc alloy and technopolymer
SUPPORT SYSTEM	4 anti-sliding feet
OPERATIONAL MODE	Touch / Continuous
SPEED SETTING	Analog
SPEED CONTROL	Electronic
STIRRING SPEED	0 - 3000 rpm
ORBITAL DIAMETER	4,5 mm
ELECTRONIC PROTECTION DEGREE CEI EN 60529	IP 42
POWER	15 W
WEIGHT	2.7 Kg (5.9 lb)
DIMENSIONS (WxHxD)	150x130x165 mm (5.9x5.1x6.5 in)



We reserve the right to make technical alterations  
We do not assume liability for errors in printing, typing or transmission

VELP Official Partner

## DESIGNED AND MANUFACTURED IN ITALY



**ITALY - HQ**  
Via Stazione 16  
20865 Usmate (MB) Italy  
Tel. +39 039 628811  
velpitalia@velp.com

**INDIA**  
velpindia@velp.com

**USA**  
155 Keyland Court, Bohemia  
NY 11716 - U.S.  
Tel. +1 631 573 6002  
velpusa@velp.com

**CHINA**  
Xinlong Rd Building 28, Lane 1333  
Shanghai city - China  
Tel. +86 180 1755 7329  
velpchina@velp.com