



# RC Series

## Heating Plates

---

Single-position and two-position heating plates with aluminum top



# Practical and Easy to use

Heating plates with aluminum top and temperature regulation. Designed for the longest lifespan and to guarantee excellent resistance to chemicals. It accepts different combinations of AluBlocks™ that can maximize temperature control and save handling time.

- Maximum temperature 370 °C
- Accepts flasks of up to 15 L volume
- Control panel is IP 42 protected from liquid spills with run-off groove (RC only)



## INSTRUMENT - CODE

RC	230 V / 50-60 Hz	<b>F20700431</b>
RC	115 V / 50-60 Hz	<b>F20710431</b>
RC2	230 V / 50-60 Hz	<b>F20700430</b>
RC2	115 V / 50-60 Hz	<b>F20710430</b>

## TECHNICAL DATA

	RC	RC2
HOUSING MATERIAL	Epoxy painted aluminum structure	Epoxy painted aluminum structure
PLATE MATERIAL	Aluminum alloy coated with a special protection	Aluminum alloy coated with a special protection
PLATE DIMENSION	135 mm	135 mm
MODELS	Single-position	2-position
TEMPERATURE RANGE	Room temp. - 370 °C	Room temp. - 370 °C
POWER INPUT	600 W	1200 W
PERMISSIBLE AMBIENT TEMPERATURE	5 - 40 °C	W
WEIGHT	1.4 Kg (3.1 lb)	3.3 Kg (7.3 lb)
DIMENSIONS (WxHxD)	165x115x280 mm (6.5x4.5x11 in)	340x90x246 mm (13.4x3.5x9.7 in)



We reserve the right to make technical alterations  
We do not assume liability for errors in printing, typing or transmission

VELP Official Partner

## DESIGNED AND MANUFACTURED IN ITALY



**ITALY - HQ**  
Via Stazione 16  
20865 Usmate (MB) Italy  
Tel. +39 039 628811  
velpitalia@velp.com

**INDIA**  
velpindia@velp.com

**USA**  
155 Keyland Court, Bohemia  
NY 11716 - U.S.  
Tel. +1 631 573 6002  
velpusa@velp.com

**CHINA**  
Xinlong Rd Building 28, Lane 1333  
Shanghai city - China  
Tel. +86 18017557329  
velpchina@velp.com